

ZINGA VS METALLISATION

ZINGA	Performance	Metallisation
Offers a cathodic protection throughout the layer, comparable to the cathodic protection of hot dip galvanising (<i>Prof. Defrancq - University of Ghent</i>).	Active Protection	Offers a cathodic protection throughout the layer.
A layer of zinc salts slowly builds up on the ZINGA surface. This creates a barrier protec- tion for the metal substrate. Next to this, a supplementary barrier protection is provided by the binder in ZINGA. The binder reduces the disintegration of the zinc.	Passive Protection	The 100 % zinc in the thermal zinc spray system is a naked zinc, without the barrier protection of the zinc particles in ZINGA.
Does not need a topcoat. A single layer of ZIN- GA is in itself a Duplex system offering on one side an ACTIVE-CATHODIC protection, on the other side a PASSIVE-BARRIER protection.	Unique System	Has porosities and the zinc in a metallisation layer is a naked zinc, therefore it is neces- sary to apply a stabilisation coating before applying one or two topcoats.
ZINGA containing 96 % of zinc remains a flexible layer, and resists to mechanical shocks by being compressed. There is no risk of disbonding (not even around the impact) within a multiple layer of ZINGA. It will never show adhesion failures. Even on thin metal ZINGA remains always the same flexible layer.	Flexibility and Brittleness	The probability exists that abrasion and/or impact (e.g. road debris), due to the brittle- ness of thermal spray coatings, results in a high incidence chipping and crack propa- gation, thereby undermining the integrity of the coating surface. Excessive cracking, at any DFT, when applied to thin/flexible metal surfaces. As a result, the thermal zinc spray flakes off and/or cracks due to metal surfa- ce flexure, thereby undermining the integrity of the coating coverage.
ZINGA will not break down at sharp corners due to its flexibility.	Sharp corners	Thermal spray coatings tend to break down at sharp corners creating target corrosion sites.
A polymerised ZINGA layer will re-liquidise upon contact with ZINGA, even after 20 years.	Reloading	After application, the zinc will not re-liquidise upon contact with a new layer.
	Application	
ZINGA is applied on a clean and rough surface to be obtained by a blasting Sa 2 $\frac{1}{2}$, 12.5 μ m with the right blasting material. A complete cle- aning to the white metal is not required, a cer- tain degree of adhering rust can be accepted, it will even increase the binding of the ZINGA to the metal surface.	Surface Preparation	The Thermal Spray process requires an ex- tremely clean white blast metal surface (Sa 3) for a proper binding Ointegrity. Extreme and absolute dry surface is required. Fully cleaned surfaces are critical to the Thermal Spray process. Moreover, white cleaning is difficult to obtain over large surface areas. The clean white metal grit blast process (to SSPC-SP-5) can also produce component distortion. Conventionally it is advised to use the Thermal Spray within 30 minutes in the open air and within 6 hours in covered areas.
A ZINGA-coating can be applied everywhere under normal conditions, regardless of tempe- rature and humidity. It does not require highly qualified personnel	Work Force	Thermal Spray coatings are very labour in- tensive and have to be performed by highly trained technicians in a workshop.



ZINGA can be applied in a complete automatic unit by spraying or dipping.	Automatisation	Thermal Spray cannot be applied automati- cally.	
ZINGA can be applied in humid circumstances and this will accelerate and improve the polyme- risation of the ZINGA layer.	Humidity	There is a poor Thermal Spray application consistency due to the sensitivity to humidi- ty of the Thermal Spray compound. Specifi- cally, during application, flow from the nozzle to the vehicle surface the Thermal Spray Aluminium can experience a chemical reac- tion causing application of a dual material compound (aluminium and aluminium oxide), instead of exclusively Aluminium. The alumi- nium oxide is highly prone to chipping which results in the forming of voids and defects in the applied coating.	
The most economic and easiest way to apply ZINGA is by dipping. Internal surfaces of the components can be treated by dipping without the need of de-gazing : ZINGA is always applied at ambient temperature.	Internal coating	It is impossible to coat internal surfaces by Thermal Spraying. (e.g. most notable vehicle components, not readily accessible unless fully disassembled).	
ZINGA is not restricted regarding time laps between surface preparation and application. ZINGA can even be applied on blow oxidation.	Time Laps in Applications	The Thermal Spray process is demanding and difficult to control in mass production (e.g. mass vehicle production) environment versus component work or smaller quanti- ties. This is primarily due to the necessity to apply the Thermal Spray compound immediately after surface cleaning and preparation, because even minimal post-cle- aning contamination on the metal surface will undermine the integrity of the Thermal Spray application.	
The film thickness can easily be measured (wet and/or dry) so that the dry layer thickness will be close to the required (uniform) thickness.	Film Thickness Control	The Thermal Spray application process is difficult to control regarding thickness uni- formity over large areas. This is particularly true for lower thickness levels	
Welding on ZINGA is possible, once the wel- ding is finished, roughened and cleaned, a new ZINGA layer over the welding will provide an all over protection.	Welding areas	Metallisation should be avoided at least to 5 cm from the welding areas, this in order not to influence the quality of the welds by zinc.	
ZINGA can be repaired and reloaded at any time. The old ZINGA surface should be clean of dust and loose rust. After a certain time repairs become invisible.	Repair	Thermal coatings are very difficult to repair. A blasting or grinding of the surface would be required and the application of the repair layer must be executed very carefully. Repairs will remain visible.	
General			
The cost price of ZINGA is comparible to the price of other protective coatings. The application costs will be relatively low.	Cost Price	Comparing the same thickness, Me- tallisation is about 30 to 40% more expensive than Zinganisation. This is if only the product and application cost are considered, all superior qualities of zinganisation left unconsidered.	
Atmospheric: 5.5 – 12.5 Immersion: 5.5 – 9.0	pH Limitations	Atmospheric: 5.5 – 9.0 Immersion: 5.5 – 9.0	